FABORY

Cross recessed raised cheese head screw Phillips DIN 7985-H Stainless steel A2 M4X65

Article number	51340.040.065
Brand	-
UBB	500633235261
UNSPSC	31161504
EAN	8715494592444
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	65 mm
Class	70
Driving features	Phillips
Head shape	Raised cheese head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	8
Full thread if L ≤	25
k	3.1
L (mm)	65
No. cross recess	2
P	0.7

Technical Drawing

