
FABORY



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Stainless steel A2 M3X45

Article number	51342.030.045
Brand	-
UBB	500633238315
UNSPSC	31161504
EAN	8715494592758
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	45 mm
Class	70
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	6
Full thread if L ≤	20
k	2.4
L (mm)	45
No. cross recess	1
P	0.5

Technical Drawing

