
FABORY



Spring-type straight pin slotted, light duty ISO 13337 Stainless spring steel 3X12MM

Article number	51431.030.012
Brand	-
UBB	500697296688
UNSPSC	31163201
EAN	8715492077035
PKG. of 1000	Full Box Only

Technical Parameters

Length	12 mm
Material	Stainless spring steel
Info	Dimensions d1 and d2 in above table are before mounting.For pins with a nominal diameter d ≥ 10 mm a single chamfer configuration is optional at the discretion of the manufacturer.The type of austenitic stainless spring steel is at the manufacturer’s discretion and may vary from the steel types stated in ISO 3506.V = minimum shear strength, double, in kN (valid for steel pins only).The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features

Standards

ISO	13337
DIN	7346

	of slotted spring-type straight pins:These pins are used to connect two or more construction elements to each other.They are highly suitable to absorb shear forces.

Technical Specification

a	0.25
a (min.)	0.25
d1 (max.)	3.5
d1 (min.)	3.3
d2 ≈	2.7
L (mm)	12
s	0.3
V	3.5

Technical Drawing

