FABORY



Grooved pin, full length taper grooved DIN 1471 Stainless steel A1 3X16MM

Article number	51585.030.016
Brand	-
UBB	500634428055
UNSPSC	31163215
EAN	8717077008816
PKG. of 500	Full Box Only

Technical Parameters

Diameter	3 mm
Length	16 mm
Material	Stainless steel
Material technical	A1
Info	V = minimum shear strength double shear in kN (valid for steel pins only).Diameter d2 is the diameter over the grooved edges (valid for steel pins only).The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11.The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

NEN	≈2602
ISO	≈8744
DIN	1471

Technical Specification

c ≈	0.4
d1	3
d2 ≈	3.25
D (mm)	3

Technical Drawing

L (mm)	16
r ≈	3
Tolerance	h9
V	6.15

