FABORY



Grooved pin, half length taper grooved DIN 1472 Stainless steel A1 2X16MM

Article number	51586.020.016
Brand	-
UBB	500634431349
UNSPSC	31163215
EAN	8717077009141
PKG. of 500	Full Box Only

Technical Parameters

Diameter	2 mm
Length	16 mm
Material	Stainless steel
Material technical	A1
Info	V = minimum shear strength double shear in kN (valid for steel pins only).Diameter d2 is the diameter over the grooved edges (valid for steel pins only).The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11.The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

NEN	≈2603
ISO	≈8745
DIN	1472

Technical Specification

c ≈	0.25
d1	2
d2 ≈	2.15
D (mm)	2

Technical Drawing

L (mm)	16
r ≈	2
Tolerance	h9
V	2.85

