FABORY



Slotted raised countersunk head tapping screw DIN 7973 C Stainless steel A2 ST2,9X6,5MM

Article number	51640.029.006
Brand	-
UBB	950352180984
UNSPSC	31161507
EAN	8715492301109
PKG. of 200	Full Box Only

Technical Parameters

Diameter	2.9 mm
Length	6.5 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

NF	E25-661 C
BS	4174
DIN	7973 C
ISO	1483 C

Technical Specification

D (mm)	2.9
dk	5.5
f ≈	0.9
k ≈	1.7
L (mm)	6.5
n	0.8
P	1.5

Technical Drawing

