FABORY



Slotted raised countersunk head tapping screw DIN 7973 C Stainless steel A2 ST2,9X25MM

Article number	51640.029.025
Brand	-
UBB	950352181552
UNSPSC	31161507
EAN	8715492301161
PKG. of 200	Full Box Only

Technical Parameters

Diameter	2.9 mm
Length	25 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

NF	E25-661 C
DIN	7973 C
BS	4174
ISO	1483 C

Technical Specification

D (mm)	2.9
dk	5.5
f ≈	0.9
k ≈	1.7
L (mm)	25
n	0.8
P	1.5

Technical Drawing

