FABORY



Slotted raised countersunk head tapping screw DIN 7973 C Stainless steel A2 ST3,5X9,5MM

Article number	51640.035.009
Brand	-
UBB	950352181719
UNSPSC	31161507
EAN	8715492301185
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	9.5 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

BS	4174
DIN	7973 C
ISO	1483 C
NF	E25-661 C

Technical Specification

D (mm)	3.5
dk	6.8
f ≈	1.2
k ≈	2.1
L (mm)	9.5
n	1
P	1.3

Technical Drawing

