FABORY



Cross recessed countersunk head tapping screw Phillips DIN 7982 C-H Stainless steel A2 ST2,2X9,5MM

Article number	51680.022.009
Brand	-
UBB	500633281455
UNSPSC	31161507
EAN	8715494597067
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	2.2 mm
Length	9.5 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

ISO	7050 CH
DIN	7982 CH
NF	E25-656

Technical Specification

D (mm)	2.2
dk	4.3
k ≈	1.3
L (mm)	9.5
No. cross recess	1
P	0.8

Technical Drawing

