FABORY



# Cross recessed countersunk head tapping screw Phillips DIN 7982 C-H Stainless steel A2 ST2,9X9,5MM

| | |
|---|---|
| Article number | 51680.029.009 |
| Brand | - |
| UBB | 950352193854 |
| UNSPSC | 31161507 |
| EAN | 8715492303837 |
| PKG. of 200 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | 2.9 mm |
| Length | 9.5 mm |
| Driving features | Phillips |
| Head shape | Countersunk head |
| Material | Stainless steel |
| Material technical | A2 |
| Thread | Self tapping thread |

## Standards

| | |
|---|---|
| NF | E25-656 |
| ISO | 7050 CH |
| DIN | 7982 CH |

## Technical Specification

| | |
|---|---|
| D (mm) | 2.9 |
| dk | 5.5 |
| k ≈ | 1.7 |
| L (mm) | 9.5 |
| No. cross recess | 1 |
| P | 1.1 |

## Technical Drawing

