FABORY



Cross recessed countersunk head tapping screw Pozidriv DIN 7982 C-Z Stainless steel A2 ST5,5X13MM

Article number	51681.055.013
Brand	-
UBB	500571348142
UNSPSC	31161507
EAN	8715494111478
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	5.5 mm
Length	13 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

DIN	7982 CZ
ISO	7050 CZ
NF	E25-656 C

Technical Specification

D (mm)	5.5
dk	10.8
k ≈	3.4
L (mm)	13
No. cross recess	3
P	1.8

Technical Drawing

