FABORY

Hexagon head bolt DIN 931 Stainless steel A4 80 M8X85

Article number	53510.080.085
Brand	-
UBB	500633303150
UNSPSC	31161620
EAN	8715494599245
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M8
Length	85 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
NEN	1555
NF	E25-112
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	85
P	1.25
s	13

Technical Drawing

