FABORY

Hexagon head bolt DIN 931 Stainless steel A4 80 M10X190

Article number	53510.100.190
Brand	-
UBB	500633304638
UNSPSC	31161620
EAN	8715494599399
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	190 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
NEN	1555
NF	E25-112
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	190
P	1.5
s	17

Technical Drawing

