FABORY



Hexagon socket head cap screw DIN 912 Stainless steel A4 80 M8X65

Article number	53570.080.065
Brand	-
UBB	500571284107
UNSPSC	31161605
EAN	8715494136303
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	65 mm
Class	80
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standards

NEN	1241
DIN	912
ASME	B18.3.1M
ISO	4762
BS	4168-1
NF	E25-125

Technical Specification

b	28
d-D	M8
dk (max.)	13
Full thread if L ≤	35
k (max.)	8
L (mm)	65
P	1.25
s	6

Technical Drawing

