FABORY



Hexagon socket head cap screw DIN 912 Stainless steel A4 80 M20X150

Article number	53570.200.150
Brand	-
UBB	500633328579
UNSPSC	31161605
EAN	8715494615648
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	150 mm
Class	80
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standards

ASME	B18.3.1M
DIN	912
NF	E25-125
ISO	4762
BS	4168-1
NEN	1241

Technical Specification

b	52
d-D	M20
dk (max.)	30
Full thread if L ≤	75
k (max.)	20
L (mm)	150
P	2.5
s	17

Technical Drawing

