FABORY



Hexagon socket head cap screw DIN 912 Stainless steel A4 80 M24X120

Article number	53570.240.120
Brand	-
UBB	500633329155
UNSPSC	31161605
EAN	8715494615709
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	120 mm
Class	80
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standards

NF	E25-125
ASME	B18.3.1M
BS	4168-1
NEN	1241
ISO	4762
DIN	912

Technical Specification

b	60
d-D	M24
dk (max.)	36
Full thread if L ≤	85
k (max.)	24
L (mm)	120
P	3
s	19

Technical Drawing

