FABORY

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M5X45

Article number	55000.050.045
Brand	-
UBB	950351845553
UNSPSC	31161620
EAN	8715492319982
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	45 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
NEN	1555
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	45
P	0.8
s	8

Technical Drawing

