FABORY

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M12X210

Article number	55000.120.210
Brand	-
UBB	951351771864
UNSPSC	31161620
EAN	8715492320889
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M12
Length	210 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
ASME	B18.2.3.1M
ISO	4014
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	210
P	1.75
s	19

Technical Drawing

