FABORY

# Hexagon head bolt DIN 931 Stainless steel A4 70 M14X65

| | |
|---|---|
| Article number | 55000.140.065 |
| Brand | - |
| UBB | 500500607014 |
| UNSPSC | 31161620 |
| EAN | 8715494054522 |
| PKG. of 50 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M14 |
| Length | 65 mm |
| Class | 70 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Stainless steel |
| Material technical | A4 |
| Thread direction | Right |
| Thread | Metric thread |
| Info | Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50. |

## Standards

| | |
|---|---|
| ASME | B18.2.3.1M |
| ISO | 4014 |
| NF | E25-112 |
| NEN | 1555 |
| DIN | 931 |

## Technical Specification

| | |
|---|---|
| b (min.): 125mmL≤200mm | 40 |
| b (min.): L200mm | 53 |
| b (min.): L≤125mm | 34 |
| d-D | M14 |
| k | 8.8 |
| L (mm) | 65 |
| P | 2 |
| s | 22 |

## Technical Drawing

