FABORY

Hexagon head bolt DIN 931 Stainless steel A4 70 M14X85

Article number	55000.140.085
Brand	-
UBB	500633332696
UNSPSC	31161620
EAN	8715494616058
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M14
Length	85 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
ASME	B18.2.3.1M
NF	E25-112
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	85
P	2
s	22

Technical Drawing

