FABORY

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M33X150

Article number	55000.330.150
Brand	-
UBB	951351781194
UNSPSC	31161620
EAN	8715492322203
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	150 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
ASME	B18.2.3.1M
ISO	4014
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91
b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	150
P	3.5
s	50

Technical Drawing

