FABORY

# Hexagon head screw DIN 933 Stainless steel A4 70 M10X25

| | |
|---|---|
| Article number | 55010.100.025 |
| Brand | - |
| UBB | 950351862954 |
| UNSPSC | 31161620 |
| EAN | 8715492324245 |
| PKG. of 100 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M10 |
| Length | 25 mm |
| Class | 70 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Stainless steel |
| Material technical | A4 |
| Thread direction | Right |
| Thread | Metric thread |
| Info | Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50. |

## Standards

| | |
|---|---|
| NF | E25-114 |
| DIN | 933 |
| ISO | 4017 |
| NEN | 1568 |
| ASME | B18.2.3.1M |

## Technical Specification

| | |
|---|---|
| d-D | M10 |
| k | 6.4 |
| L (mm) | 25 |
| P | 1.5 |
| s | 17 |

## Technical Drawing

