FABORY



Hexagon socket head cap screw DIN 912 Stainless steel A4 70 M1,6X8

Article number	55050.016.008
Brand	-
UBB	500571288736
UNSPSC	31161605
EAN	8715494141130
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M1.6
Length	8 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NEN	1241
ASME	B18.3.1M
NF	E25-125
BS	4168-1
DIN	912
ISO	4762

Technical Specification

b	15
d-D	M1.6
dk (max.)	3
Full thread if L ≤	16
k (max.)	1.6
L (mm)	8
P	0.35
s	1.5

Technical Drawing

