FABORY



# Hexagon socket head cap screw DIN 912 Stainless steel A4 Min.50 M1,6X16

| | |
|---|---|
| Article number | 55050.016.016 |
| Brand | - |
| UBB | 500571289072 |
| UNSPSC | 31161605 |
| EAN | 8715494141161 |
| PKG. of 500 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M1.6 |
| Length | 16 mm |
| Class | Min.50 |
| Driving features | Hexagon socket |
| Head shape | Cylindrical head |
| Material | Stainless steel |
| Material technical | A4 |
| Thread direction | Right |
| Thread | Metric thread |
| Info | Sizes with a diameter M20 are minimal property class 50. |

## Standards

| | |
|---|---|
| NEN | 1241 |
| ISO | 4762 |
| DIN | 912 |
| NF | E25-125 |
| ASME | B18.3.1M |
| BS | 4168-1 |

## Technical Specification

| | |
|---|---|
| b | 15 |
| d-D | M1.6 |
| dk (max.) | 3 |
| Full thread if L ≤ | 16 |
| k (max.) | 1.6 |
| L (mm) | 16 |
| P | 0.35 |
| s | 1.5 |

## Technical Drawing

