FABORY



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M3X60

Article number	55110.030.060
Brand	-
UBB	500571381879
UNSPSC	31161504
EAN	8715494134750
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	60 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

DIN	963
ASME	≈B18.6.7M
ISO	≈2009
BS	≈4183
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	60
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

