FABORY



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M4X70

Article number	55110.040.070
Brand	-
UBB	500571382299
UNSPSC	31161504
EAN	8715494134798
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	70 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NEN	≈2370
BS	≈4183
ISO	≈2009
NF	≈E25-123
DIN	963
ASME	≈B18.6.7M

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if L ≤	25
k (max.)	2.2
L (mm)	70
n	1
P	0.7
t (min.)	0.8

Technical Drawing

