FABORY



Slotted cheese head screw DIN 84 Stainless steel A4 M3X4

Article number	55120.030.004
Brand	-
UBB	500571386829
UNSPSC	31161504
EAN	8715494128063
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	4 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈1207
NF	≈E25-127
DIN	84
BS	≈4183
NEN	≈1602

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	5.5
Full thread if L ≤	30
k (max.)	2
L (mm)	4
n	0.8
P	0.5
t (min.)	0.85

Technical Drawing