FABORY



Slotted cheese head screw DIN 84 Stainless steel A4 70 M3,5X8

Article number	55120.035.008
Brand	-
UBB	500571387405
UNSPSC	31161504
EAN	8715494128124
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3.5
Length	8 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

BS	≈4183
NEN	≈1602
DIN	84
ASME	≈B18.6.7M
NF	≈E25-127
ISO	≈1207

Technical Specification

d-D	M3.5
Thread length (min.)	38
dk (max.)	6
Full thread if L ≤	40
k (max.)	2.4
L (mm)	8
n	1
P	0.6
t (min.)	1

Technical Drawing