FABORY



Slotted cheese head screw DIN 84 Stainless steel A4 70 M4X18

Article number	55120.040.018
Brand	-
UBB	500571388239
UNSPSC	31161504
EAN	8715494128209
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	18 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NEN	≈1602
BS	≈4183
ISO	≈1207
DIN	84
NF	≈E25-127
ASME	≈B18.6.7M

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	7
Full thread if L ≤	40
k (max.)	2.6
L (mm)	18
n	1.2
P	0.7
t (min.)	1.1

Technical Drawing