FABORY



# Slotted cheese head screw DIN 84 Stainless steel A4 70 M5X100

| | |
|---|---|
| Article number | 55120.050.100 |
| Brand | - |
| UBB | 950353474006 |
| UNSPSC | 31161504 |
| EAN | 8715492335388 |
| PKG. of 200 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M5 |
| Length | 100 mm |
| Class | 70 |
| Driving features | Slotted |
| Head shape | Cylindrical head |
| Material | Stainless steel |
| Material technical | A4 |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| ASME | ≈B18.6.7M |
| NEN | ≈1602 |
| NF | ≈E25-127 |
| BS | ≈4183 |
| ISO | ≈1207 |
| DIN | 84 |

## Technical Specification

| | |
|---|---|
| d-D | M5 |
| Thread length (min.) | 38 |
| dk (max.) | 8.5 |
| Full thread if L ≤ | 40 |
| k (max.) | 3.3 |
| L (mm) | 100 |
| n | 1.2 |
| P | 0.8 |
| t (min.) | 1.3 |

## Technical Drawing