
FABORY



Slotted pan head screw DIN 85 Stainless steel A4 70 M3X40

Article number	55140.030.040
Brand	-
UBB	500571517928
UNSPSC	31161504
EAN	8715494096690
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	40 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-128
ASME	≈B18.6.7M
ISO	≈1580
DIN	85
NEN	≈1603
BS	≈4183

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if L ≤	30
k (max.)	1.8
L (mm)	40
n	0.8
P	0.5
t (min.)	0.7

Technical Drawing

