
FABORY



Slotted pan head screw DIN 85 Stainless steel A4 70 M6X20

Article number	55140.060.020
Brand	-
UBB	950353336999
UNSPSC	31161504
EAN	8715492336224
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	20 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NEN	≈1603
ASME	≈B18.6.7M
BS	≈4183
ISO	≈1580
DIN	85
NF	≈E25-128

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	12
Full thread if L ≤	40
k (max.)	3.6
L (mm)	20
n	1.6
P	1
t (min.)	1.4

Technical Drawing

