FABORY

Hexagon nut MF DIN 934 Stainless steel A4 70 M12X1,25

Article number	55160.120.125
Brand	-
UBB	950355747482
UNSPSC	31161727
EAN	8715492336422
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M12
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric fine thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

DIN	934
NF	E25-401
NEN	1560

Technical Specification

d-D	M12
m	10
P	1.25
s	19

Technical Drawing

