FABORY



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M4X35

Article number	55210.040.035
Brand	-
UBB	950353313139
UNSPSC	31161504
EAN	8715492337085
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	35 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-124
DIN	964
BS	≈4183
ASME	≈B18.6.7M
ISO	≈2010
NEN	≈2371

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	35
n	1
P	0.7
t (min.)	1.6

Technical Drawing

