FABORY



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M6X10

Article number	55210.060.010
Brand	-
UBB	950353314384
UNSPSC	31161504
EAN	8715492337320
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	10 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-124
NEN	≈2371
DIN	964
ASME	≈B18.6.7M
BS	≈4183
ISO	≈2010

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	10
n	1.6
P	1
t (min.)	2.4

Technical Drawing

