

## Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M6X60



Article number	55210.060.060
Brand	-
UBB	950353315290
UNSPSC	31161504
EAN	8715492337429
PKG. of 200	Full Box Only

### Technical Parameters

Diameter	M6
Length	60 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

### Standards

ASME	≈B18.6.7M
ISO	≈2010
NEN	≈2371
DIN	964
NF	≈E25-124
BS	≈4183

### Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	60
n	1.6
P	1
t (min.)	2.4

### Technical Drawing

