FABORY



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M8X60

Article number	55210.080.060
Brand	-
UBB	950353316025
UNSPSC	31161504
EAN	8715492337542
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	60 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-124
ISO	≈2010
NEN	≈2371
ASME	≈B18.6.7M
BS	≈4183
DIN	964

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
f ≈	2
Full thread if L ≤	40
k (max.)	4
L (mm)	60
n	2
P	1.25
t (min.)	3.2

Technical Drawing

