FABORY



Hexagon socket set screw with dog point DIN 915 Stainless steel A4 M4X12

Article number	55230.040.012
Brand	-
UBB	500571742161
UNSPSC	31161518
EAN	8715494117531
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	12 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A4
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

ASME	B18.3.6M
NF	E27-182
ISO	4028
BS	4168-4
NEN	2344
DIN	915

Technical Specification

d-D	M4
dp (max.)	2.5
L (mm)	12
P	0.7
s	2
t (min.)	1.5
z long (min.)	2
z long if L ≥	8
z short (min.)	1

Technical Drawing

