FABORY



Hexagon socket set screw with dog point DIN 915 Stainless steel A4 M8X30

Article number	55230.080.030
Brand	-
UBB	500571744480
UNSPSC	31161518
EAN	8715494117760
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	30 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A4
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

BS	4168-4
ASME	B18.3.6M
NEN	2344
DIN	915
ISO	4028
NF	E27-182

Technical Specification

d-D	M8
dp (max.)	5.5
L (mm)	30
P	1.25
s	4
t (min.)	3
z long (min.)	4
z long if L ≥	12
z short (min.)	2

Technical Drawing

