FABORY



# Hexagon socket set screw with dog point DIN 915 Stainless steel A4 M10X25

| | |
|---|---|
| Article number | 55230.100.025 |
| Brand | - |
| UBB | 500571744977 |
| UNSPSC | 31161518 |
| EAN | 8715494117814 |
| PKG. of 100 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M10 |
| Length | 25 mm |
| Driving features | Hexagon socket |
| Material | Stainless steel |
| Material technical | A4 |
| Thread direction | Right |
| Point | Dog |
| Thread | Metric thread |
| Info | These set screws are designed for pressure loads and are not suitable for tensile- or shear loads. |

## Standards

| | |
|---|---|
| NF | E27-182 |
| ASME | B18.3.6M |
| ISO | 4028 |
| DIN | 915 |
| NEN | 2344 |
| BS | 4168-4 |

## Technical Specification

| | |
|---|---|
| d-D | M10 |
| dp (max.) | 7 |
| L (mm) | 25 |
| P | 1.5 |
| s | 5 |
| t (min.) | 4 |
| z long (min.) | 5 |
| z long if L ≥ | 16 |
| z short (min.) | 2.5 |

## Technical Drawing

