FABORY



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A4 M3X22

Article number	55300.030.022
Brand	-
UBB	500633405120
UNSPSC	31161504
EAN	8715494623315
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	22 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

DIN	965
NF	≈E25-119-1
ISO	≈7046-1

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	22
No. cross recess	1
P	0.5

Technical Drawing

