
FABORY



T-head bolt type 28/15 Stainless steel A4 M10X20

Article number	55740.100.020
Brand	-
UBB	500634383169
UNSPSC	31161638
EAN	8715494634458
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	20 mm
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

Technical Specification

b1	10
b2	22.5
d-D	M10
k	4.5
L (mm)	20

Technical Drawing

