
FABORY



Glass-fiber reinforced epoxy Permaglas ME 730 M24

Article number	56052.240.001
Brand	-
UBB	950355856291
UNSPSC	31161731
EAN	8715492860118
PKG. of 4	Full Box Only

Technical Parameters

Diameter	M24
Color	Beige
Driving features	Hexagon
Material	Glass-fiber reinforced epoxy
Material technical	Permaglas ME 730
Thread direction	Right
Thread	Metric thread
Info	Special features PERMAGLAS ME 730:Glass-fiber reinforced epoxyTemperature resistant –270°C up to +155°CLight weight (density 1,85 g/cm³)Corrosion resistant, highly UV- and weather resistantResistant to aggressive chemicals and gasesProvides electrical and thermal insulationNon-magneticBetter mechanical

Standards

properties than e.g. Polyamide

Technical Specification

d-D	M24
m	24
P	3
s	36

Technical Drawing

