FABORY



KIPP Indexing plungers, non-lockout type, without locknut Metric fine thread Stainless steel 1.4305, pin not hardened, stainless steel grip 8MM

Article number	58684.000.008
Brand	-
UBB	500690013650
UNSPSC	31162807
EAN	4059245010578
PKG. of 2	Full Box Only

Technical Parameters

D1_MM	16mm
Material	Stainless steel
Material technical	1.4305
Thread	Metric fine thread
Info	Material: Stainless steel. Threaded sleeve 1.4305. Indexing pin 1.4305. Mushroom knob 1.4305, electrolytic-polish.Version: Bright. Indexing pin not hardened, ground.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged.

Standards

Technical Specification

Technical Drawing

D	8
D1	16
D2	33
F1 = springiness beginning in N	15
F2 = springiness end in N	35
F x 30°	2.3
H	8
L1	26
L2	10
L3	23
L	77
P	1.5
SW1	19

