
FABORY



FISCHER Aircrete anchor Plastic Nylon (polyamide) GB 10

Article number	63300.100.001
Brand	-
UBB	950372003596
UNSPSC	31162103
EAN	4006209504925
PKG. of 20	Full Box Only

Technical Parameters


Color	Grey
Material	Plastic
Approval	Zulassung
Type no.	GB
Info	* Tensile zone of cellular concrete roof- and ceiling panels acc. DIN 4223Allowable loads are valid for Fischer safety screws.For the design the complete approval has to be considered.

Standards

Technical Specification

Cellular concrete ≥ P3,3 (GB3,3)	0.5
Cellular concrete ≥ P4,4 (GB4,4)	0.6
Cellular concrete ≥ PB2, PP2 (G2)	0.25
Cellular concrete ≥ PB3,3 (GB3,3)*	0.5
Cellular concrete ≥ PB4, PP4 (G4)	0.6
Drill depth (min.)	65

Technical Drawing



Drill ø	10
L (mm)	55
Screw ø	7
Type	GB 10