
FABORY



FISCHER Turbo anchor FTP steel Steel Plain M10

Article number	63309.100.001
Brand	-
UBB	500501458177
UNSPSC	31162103
EAN	4006209784174
PKG. of 25	Full Box Only

Technical Parameters


Diameter	M10
Material	Steel
Surface treatment	Plain
Type no.	FTP
Info	Tools, see following pages.Allowable loads in kN are valid for screws with specified diameters.Allowable load includes the safety factor 5.Drill ø values between brackets applied to cellular concrete class ≥ 5,0 N/mm2.

Standards

Technical Specification

Cellular concrete PB2, PP2 (≥ 2,5 N/mm2)	0.6
Cellular concrete PB4, PP4 (≥ 5,0 N/mm2)	0.7
Cellular concrete PB6, PP6 (≥ 7,5 N/mm2)	0.9
d-D	M10
Depth of drilled hole to deepest point	80

Technical Drawing



Drill ø	12
L (mm)	70
Plasterboard	0.65
Screw ø	M10
Screw-in depth (max.)	30