
FABORY



RAWL Expansion shield anchor bolt projecting version Steel Zinc plated 5.8 M6X60

Article number	65435.060.060
Brand	-
UBB	952351395738
UNSPSC	31162400
EAN	5906675283630
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M6
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	do = Nominal diameter of drill bit.fs = Washer outside diameter.s (Ws) = Width across flats.Tinst = Tightening torque in Nm.df = Anchor diameter.hmin. = Minimal thickness of concrete member.dd (ho) = Recommended drilling depth.tfix = Grip range.hef = Effective anchorage depth.Smin. = Minimal spacing.Cmin. = Minimal edge distance.

Standards

Technical Specification

Cmin.	53

Technical Drawing

d-D	M6
df	6.5
do	12
fs	12.5
hef	45
hmin	100
ho	50
kN	3.33
L (mm)	115
s	10
Smin.	35
tfix(max.)	60
Tinst	6.5

