
FABORY



RAWL Expansion shield anchor bolt projecting version Steel Zinc plated 5.8 M8X10

Article number	65435.080.010
Brand	-
UBB	952351395811
UNSPSC	31162400
EAN	5906675283654
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M8
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	do = Nominal diameter of drill bit.fs = Washer outside diameter.s (Ws) = Width across flats.Tinst = Tightening torque in Nm.df = Anchor diameter.hmin. = Minimal thickness of concrete member.dd (ho) = Recommended drilling depth.tfix = Grip range.hef = Effective anchorage depth.Smin. = Minimal spacing.Cmin. = Minimal edge distance.

Standards

Technical Specification

Cmin.	60

Technical Drawing

d-D	M8
df	9
do	14
fs	17
hef	50
hmin	100
ho	55
kN	4.17
L (mm)	75
s	13
Smin.	40
tfix(max.)	10
Tinst	15

