
FABORY



Self-cutting threaded insert type 302 Stainless steel 1.4305 M4X8

Article number	71566.040.001
Brand	-
UBB	950355789138
UNSPSC	31162802
EAN	8715492910288
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M4
Length	8 mm
Material	Stainless steel
Material technical	A1
Thread	Metric thread
Type no.	302
Info	Type 302 inserts may be used in materials with a tensile strength up to 320 MPa.Drill depth (min.) = Minimum borehole depth for blind holes.

Standards

Technical Specification

d-D	M4
d1	M4
d2	6.5
Drill depth (min.)	10
L (mm)	8
P (d1)	0.7
P (d2)	0.75

Technical Drawing

