
FABORY



Self-cutting threaded insert type 302 Stainless steel 1.4305 M20X27

Article number	71566.200.001
Brand	-
UBB	500644970971
UNSPSC	31162802
EAN	8717077046733
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	27 mm
Material	Stainless steel
Material technical	A1
Thread	Metric thread
Type no.	302
Info	Type 302 inserts may be used in materials with a tensile strength up to 320 MPa.Drill depth (min.) = Minimum borehole depth for blind holes.

Standards

Technical Specification

d-D	M20
d1	M20
d2	26
Drill depth (min.)	32
L (mm)	27
P (d1)	2.5
P (d2)	1.5

Technical Drawing

